




## Connection Information

Type: **7108**



**Further Information:**

10W Output Transformer for use with 12BH7 valves.


$Z_{(Primary)}$ : 7.5k $\Omega$  each half

$Z_{(Secondary)}$ : 600 $\Omega$



## Connection Information

Type: **7108 (Pre-2000, now superseded)**



**Further Information:**

10W Output Transformer for use with 12BH7 valves.

$Z_{\text{(Primary)}}$ : 7.5k $\Omega$  each half

$Z_{\text{(Secondary)}}$ : 600 $\Omega$

Primary tapped at 13% (Brown), 32% (Pink) and 60% (Grey) from CT.